

DX1002-T

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 12 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.





DX1002-T

Drive Input	Electric or Pneumatic			
Connection Ports	3/8"BSP In & Out			
Flow Indicator	Visual			
Suggested System Volume	Up to 9000l @ 32cSt			
Particulate Removal	From 0,1 μ			
Weight	25 kg			
Dimensions	H 916 mm x D 300 mm x L 550 mm			
Material	SS316			
DXO Cartridge QTY	2			

Flow Rate varies depending on viscosity, pressure and temperature

Approx	32 CSt	46 CSt	68 CSt	100 cSt	220 CSt	320 CSt	460 CSt
flow at 2.7 bar:	2.5 l/min	2.0 l/min	16 l/min	1.2 l/min	0.8 L/min	0.4 L/min	0.2 L/min
Oil Volume	9000ltrs	7000ltrs	6000ltrs	4800ltrs	3600ltrs	1600ltrs	800ltrs




ایران-تهران-خیابان پاسداران بهستان هشتم پلاک ۱ - برج آبتین، طبقه٤ - واحد ۹ ۴ شماره تماس: ۲۲ ۷۳۶۶۰۰۰ info@rnaco.com








DX1002-T

General Arrangement









DXO Cartridge

Contamination capacity:	Up to 4.5kg per DXO		
Water absorption, free and bound:	2600ml		
Material insert:	PP Cellulose mix		





