

DX-1003-W

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 3 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.





b	"	4	.o	v	3	·V	v

Drive Input	Electric or Pneumatic
Connection Ports	3/8"BSP In & Out
Flow Indicator	Visual
Suggested System Volume	Up to 13,500l @ 32cSt
Particulate Removal	From 0.1 μ
Weight	20 kg
Measure	H 1008 mm x D 261 mm x L 442 mm
Material	SS316
DXO Cartridge QTY	3

Flow Rate varies depending on viscosity, pressure and temperature

Approx	32 cSt	46 cSt	68 cSt	100 cSt	220 cSt	320 cSt	460 cSt
flow at 2.7 bar:	3.75 1∕min	3.0 l/min	2.4 L/min	1.8 l/min	1.2 l/min	0.6 L/min	0.3 L/min
Oil Volume	13500ltrs	10500ltrs	9000ltrs	7200ltrs	5400ltrs	2400ltrs	1200ltrs




ایران-تهران-خیابان پاسداران بهستان هشتم پلاک ۱ - برج آبتین، طبقه٤ - واحد ۹ ۴ شماره تماس: ۲۱ ۷۳۶۶۰۰۰ info@rnaco.com








DX1003-W

General Arrangement









DXO Cartridge

Contamination capacity:	Up to 4.5kg per DXO		
Water absorption, free and bound:	2600ml		
Material insert:	PP Cellulose mix		





