



# DELTA-XERO

THE FUTURE IS SYSTEM RELIABILITY

## DX1009-T

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 12 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.



### DX1009-T

Drive Input	Electric or Pneumatic
Connection Ports	3/8" BSP In & Out
Flow Indicator	Visual
Suggested System Volume	Up to 40500ltrs @ 32cSt
Particulate Removal	From 0.1 μ
Weight	70 kg
Dimensions	H 1158 mm x D 300 mm x L 1100 mm
Material	SS316
DXO Cartridge QTY	9

Flow Rate varies depending on viscosity, pressure and temperature

Approx flow at 2.7 bar:	32 cSt	46 cSt	68 cSt	100 cSt	220 cSt	320 cSt	460 cSt
	7.8 l/min	6.75 l/min	5.65 l/min	4.65 l/min	3.5 l/min	1.75 l/min	1.25 l/min
Oil Volume	40500ltrs	31500ltrs	27000ltrs	21600ltrs	16200ltrs	7200ltrs	3600ltrs





ایران - تهران - خیابان پاسداران بهستان هشتم  
پلاک ۱ - برج آبتین، طبقه ۴ - واحد ۹  
شماره تماس: ۰۲۱ ۷۳۶۴۰۰۰  
info@rnaco.com



نماینده فروش و خدمات پس از فروش DELTA-XERO در ایران

## General Arrangement



### DXO Cartridge

Contamination capacity:	Up to 4.5kg per DXO
Water absorption, free and bound:	2500ml
Material insert:	PP Cellulose mix



ایران - تهران - خیابان پاسداران بهستان هشتم  
پلاک ۱ - برج آبتین، طبقه ۴ - واحد ۹  
شماره تماس: ۰۲۱ ۷۳۶۴۰۰۰  
info@rnaco.com